



### 1" O.D. heavy duty stainless steel grab bar with exposed mounting:

#### Product Materials

**FLANGES:** 3/8" dia. 11 gauge stainless steel, with exposed surfaces in architectural satin finish.

**TUBING:** 1" O.D. 18 gauge stainless steel, seamless construction with exposed surfaces in architectural satin finish. Bent ends of tubing pass thru the flanges and are welded into a single structural unit for maximum strength. Intermediate supports are contour cut and joined by welding to form an integral part of the grab bar. All welds ground and polished to blend. Mandrel bending process maintains uniform bar diameter. Return provides 1 1/2" standard safety clearance between wall and bar.

#### Strength

When properly mounted, all Bradley heavy duty grab bar systems meet or exceed the requirements of ANSI Standard A117.1, the ADA and ABA Accessibility Guidelines for Buildings and Facilities (ADAAG), and the Uniform Federal Accessibility Standard (UFAS). All standard (non-bariatric) grab bars are rated to support up to 250 pounds. Please see Bradley's website for more information on all bariatric grab bar configurations.

#### Installation

For instructions on installation, warnings and maintenance, please visit [www.bradleycorp.com](http://www.bradleycorp.com).

#### Optional Features

| Features   | Suffix |
|--|--------|
| <input type="checkbox"/> Safety-grip finish                    | -2     |
| <input type="checkbox"/> High-polish finish                    | -4     |
| <input type="checkbox"/> Safety grip with high-polished finish | -7     |

#### Guide Specification

Grab bar shall be satin finish stainless steel with exposed mounting flanges in sizes and configurations as indicated. Install with Bradley Mounting Kits as indicated.

